# **VSO® Low Flow**

## Thermally Compensated Proportional Valve



The VSO® Low Flow valve provides enhanced flow control for applications where precise control flow control is required between 0 - 500 sccm. Like the VSO® miniature proportional valve, the VSO® Low Flow miniature proportional valve provides precise flow control of gas in proportion to input current. The valve can be controlled with either DC current or pulse width modulation along with closed loop feedback to deliver optimal system performance. Together with its ability to provide precise control over a wide range of media, the VSO® Low Flow miniature proportional valve is ideally suited for manufacturers of Gas Chromatography and Mass Spectrometry equipment.

### **Typical Applications**

- Gas Chromatography
- Mass Spectrometry
- Pressure & Flow Control
- Mass Flow Control

#### **Features**

- Enables precise low flow (0 500 sccm) control for improved instrument accuracy
- Thermally compensated to maintain precise flow over a wide range of media
- Computer automated calibration and serialization for performance traceability
- Cleaned for Oxygen and Analytical Service use
- Proven performance tested to 10 million life cycles
- RoHS compliant

# Product Specifications Physical Properties

# Valve Type:

2-Way Normally Closed

#### Media:

Air, argon, helium, hydrogen, methane, nitrogen, oxygen, & others

#### **Operating Environment:**

32 to 131°F (0 to 55°C)

#### **Storage Temperature:**

-40 to 158°F (-40 to 70°C)

#### Length:

1.79 in (45.3 mm)

#### Width:

0.63 in (15.9 mm)

#### Height:

0.67 in (17.0 mm)

#### **Porting:**

Manifold mount

#### Weight:

2.2 oz (63 grams)

#### **Physical Properties**

#### **Internal Volume:**

0.031 in<sup>3</sup> (0.508 cm<sup>3</sup>)

#### Filtration:

5 Micron (Customer Supplied)

#### Flow Direction:

Inlet Port Port 2
Outlet Port Port 1

#### Oxygen and Analytically Clean:

Standard

#### Electrical

### Power:

1.0 Watt maximum

#### Voltage:

See Table 2

#### **Electrical Termination:**

18" (45.7 cm) Wire Leads

#### **Wetted Materials**

**Body:** 360 H02 Brass, 300 Series Stainless Steel

#### Stem Base

430 FR Stainless Steel and Brass 360 HT

#### **All Others:**

FKM; 430 FR Stainless Steel; 300 Series Stainless Steel

#### Performance Characteristics

### Leak Rate:

The leakage shall not exceed the following values:

Internal 0.2 SCCM of He with a differential pressure of 1 psid, 25 psid and 150 psid

External 0.016 SCCM of He at 150 psi

#### Pressure:

0 to 150 psi (10.34 bar) See Table 1

### Vacuum:

0-27 in Hg (0-686 mm Hg)

#### **Orifice Size:**

0.003" (0.076 mm)

#### **Hysteresis:**


7% of full scale current (Typical) 15% of full scale current (Max)

VSO is a registered trademark of Parker Hannifin Corporation.




# VS0® Low Flow Thermally Compensated Proportional Valve Typical Flow Curve





Model L3 - 0.003" (0.076 mm) Orifice Pressure vs Flow Curve



# **Pressure and Flow Capabilities**

Table 1





# VS0® Low Flow Thermally Compensated Proportional Valve

# **Pneumatic Interface**


# VS0® Low Flow Manifold Mount



# **Mechanical Integration**


**Dimensions** 

### VSO® Low Flow Basic Valve Dimensions



# **Electrical Interface**

Coil Type: 18" Wire Lead



# **Electrical Requirements**

Table 2


Minimum Available Voltage (VDC)	Nominal Coil Resistance @ 20°C (Ohms)	Input Current for Full Flow (mA)
6.5	47	130
8.0	68	115
12	136	80
18	274	60
24.0	547	43



# VS0® Low Flow Thermally Compensated Proportional Valve

## Installation and Use

### Typical Valve Set-up



#### **Valve Electrical Control**


#### **Basic Control:**

The VSO® Low Flow valve can be controlled by either voltage or current; however, it is highly recommended that current control be employed to ensure the most repeatable valve flow performance.

#### **PWM Control:**

For PWM control, the signal applied to the valve should have a frequency between 5-12kHz. Optimum frequency will be application dependent.

### Suggested VSO® Low Flow Current Driver Schematic



This simple current driver circuit draws only 1 mA at the input control (0-5VDC) and provides control for any VSO® Low Flow configuration regardless of valve voltage or resistance.

Table 3 (below) describes the recommended R1 and R2 resistor values based upon the full shut-off current.

Table 3: Selectable Resistor Values for a Low Current (1mA)
LM358-Based Current Driver


Voltage Supplied		Nominal Coil			
to Valve Coil	Valve Drive	Resistance @	Input Current for	R1	R2
(Reference)	Voltage (VDC)	20°C (Ohms)	Full Flow (mA)	(Ohms)	(Ohms)
6.5	8.5	47	130	4990	102
8.0	10.0	68	115	4990	73
12.0	14.0	136	80	5100	34.4
18.0	20.0	274	60	8560	28.7
24.0	26.0	547	43	8560	15.4



# VS0® Low Flow Thermally Compensated Proportional Valve Installation and Use

### Manifold & O-Ring Dimensions & Design

Not shipped with valves.




### **Accessories**

#### O-Ring (Manifold Seal) Dimensions

190-007024-002 (2 required for each valve)

I.D. = Ø.114 ±.005 [Ø2.90 ±0.13] W = .070 ±.003 [1.78 ±0.08] O.D. = Ø.254 [Ø6.45] REFERENCE



## Screw 4-40 x 5/8" Pan Head, Phillips

191-000115-010 (2 required for each valve)



# **Ordering Information**

Sample Part ID	910 -	. 0	0020	0	Е	001
Description	Series -	Body / Elastomer	Model Number	Electrical Interface	-	Coil Voltage*/ Resistance
Options			VSO Low Flow, 0.003" (0.076 mm) Orifice	0: Wire Leads, 18" (45.7 cm)		001: 6.5 VDC / 47 OHMS 002: 8 VDC / 68 OHMS 003: 12 VDC / 136 OHMS 004: 18 VDC / 274 OHMS 007: 24 VDC / 547 OHMS ** Maximum voltage for continuous full flow, ambient temperature 55°C

Accessories

190-007024-002: O-ring, FKM, 0.114" ID x 0.070" Thick\*

\*Not supplied with the valve. Used as a seal between the valve body and manifold.

\*Not supplied with the valve. Used to mount the valve to a manifold.

NOTE: In order to provide the best possible solution for your application, please provide the following requirements when contacting Applications Engineering:



- Media, Inlet & Outlet Pressures
- Minimum Required Flow Rate
- System Supply Voltage
- Media & Ambient Temperature Range

Please click on the Order On-line button (or go to www.parker.com/precisionfluidics/lowflow) to configure your VSO® Low Flow Thermally Compensated Proportional Valve. For more detailed information, visit us on the Web, or call and refer to Performance Spec. #790-002160-002 and Drawing #890-003022-022.

PPF-MPV-002/US June 2017



# **NOTES**

